



Devonshire®
24-1/4" rectangular pedestal bathroom sink
K-2286-4

Features

- 4" (102 mm) centerset faucet holes
- Oval basin
- Overflow drain
- Combination consists of the K-2287-4 basin and the K-2288 pedestal
- Coordinates with other products in the Devonshire collection

Material

- Vitreous china

Installation

- Pedestal

Recommended Products/Accessories

- K-7605-P Angle Supply with Stop (pair)
- K-8998 P-Trap
- K-23726 Drain treatment
- K-23725 Cast iron cleaner

Optional Products/Accessories

- 1041816 Hardware kit, Hollow Wall

Included Components

- 52204 Mounting Bag for Pedestal Lavatory
- 63069 Leveling Pads




Codes/Standards

- ASME A112.19.2/CSA B45.1
- IAPMO Certification

KOHLER® Vitreous China Bathroom Sink Lifetime Limited Warranty

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Basin configuration:	Single Bowl
Center(s):	4" (102 mm)
Bowl area:	Length: 17" (432 mm) Width: 12" (305 mm) Water depth: 4-7/8" (124 mm)
With overflow:	Yes
Number of deck holes:	3
Faucet hole(s):	1-1/4" (32 mm)
Drain hole:	1-3/4" (44 mm)

Notes

Install this product according to the installation instructions.