



Devonshire®
24-1/4" rectangular pedestal bathroom sink
K-2286-8

Features

- 8" (203 mm) widespread faucet holes
- Oval basin
- Overflow drain
- Combination consists of the K-2287-8 basin and the K-2288 pedestal
- Coordinates with other products in the Devonshire collection

Material

- Vitreous china

Installation

- Pedestal

Recommended Products/Accessories

- K-7605-P Angle Supply with Stop (pair)
- K-8998 P-Trap
- K-23726 Drain treatment
- K-23725 Cast iron cleaner

Optional Products/Accessories

- 1041816 Hardware kit, Hollow Wall

Included Components

- 52204 Mounting Bag for Pedestal Lavatory
- 63069 Leveling Pads



Codes/Standards


- ASME A112.19.2/CSA B45.1
- IAPMO Certification

KOHLER® Vitreous China Bathroom Sink Lifetime Limited Warranty

See website for detailed warranty information.



Devonshire®
 24-1/4" rectangular pedestal bathroom sink
K-2286-8



Technical Information

All product dimensions are nominal.

- Basin configuration: Single Bowl
- Center(s): 8" (203 mm)
- Bowl area: Length: 17" (432 mm)
 Width: 12" (305 mm)
 Water depth: 4-7/8" (124 mm)
- With overflow: Yes
- Number of deck holes: 3
- Faucet hole(s): 1-3/8" (35 mm)
- Drain hole: 1-3/4" (44 mm)

Notes

Install this product according to the installation instructions.