



# Devonshire®

## Pedestal Bathroom Sink Basin

### K-2295-8

#### Features

- 8" (203 mm) centerset faucet holes.
- Oval basin.
- Overflow drain.
- Combines with the K-2288 pedestal to create the K-2294-8 Devonshire pedestal sink.
- Coordinates with other products in the Devonshire collection.

#### Material

- Vitreous china.

#### Installation

- Pedestal sink.

#### Recommended Products/Accessories

- K-2288 Bathroom Sink Pedestal
- K-23726 Drain treatment
- K-23725 Cast iron cleaner



#### Codes/Standards












ASME A112.19.2/CSA B45.1

#### KOHLER® One-Year Limited Warranty

See website for detailed warranty information.

#### Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
	0	White
	96	Biscuit
	47	Almond
	NY	Dune
	95	Ice™ Grey
	G9	Sandbar
	K4	Cashmere
	58	Thunder™ Grey
	7	Black Black™
	71	Seafoam Green
	89	Desert Bloom

No image available.

This product is a component and not intended to be a standalone installation.

## Technical Information

All product dimensions are nominal.

Bowl configuration:	Single
Installation:	Pedestal
Bowl area:	Length: 17" (432 mm) Width: 12" (305 mm) With overflow: Yes Water depth: 4-7/8" (124 mm)
Bowl area:	With overflow: Yes
With overflow:	Yes
Number of deck holes:	3
Faucet hole spacing:	8" (203 mm)
Faucet hole(s):	1-3/8" (35 mm)
Drain hole:	1-3/4" (44 mm)

## Notes

Install this product according to the installation instructions.