

### Features

- Nondiverter spout
- 7-1/2" (191 mm) spout reach
- 11.0 gpm (41.6 lpm) maximum bath faucet flow rate at 45 psi (3.1 bar)
- Laminar flow delivers a graceful stream of water
- Coordinates with Components faucets, accessories, and showering components to complete your bathroom
- For use with Components™ Lever, Oyl, or Industrial faucet handles (sold separately)

### Material

- Premium metal construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing

### Installation

- Deck-mount
- G 1/2 inlet connection

### Required Products/Accessories

- K-77990-4 deck-mount bath faucet handles with valve
- or
- K-77990-8 deck-mount bath faucet handles with valve
- or
- K-77990-9 deck-mount bath faucet handles with valve

### Recommended Products/Accessories

- K-23723 Faucet cleaner




### Codes/Standards

AS 3718

### KOHLER® Faucet Lifetime Limited Warranty

See website for detailed warranty information.



### Technical Information

All product dimensions are nominal.

#### Faucet:

Flow rate: 11 gal/min (41.6 l/min)  
 Pressure: 45 psi (3.1 bar)  
 Drain included: No

### Notes

Install this product according to the installation instructions.