Crue™ | K-22972

Pull-down kitchen sink faucet with three-function sprayhead

Features

- Three-function pull-down sprayhead with touch control allows you to switch between aerated stream, ring spray and Boost technology
- Boost technology increases the flow rate by 30% with the press of a button. Use Boost with stream for faster filling or with ring spray for more powerful cleaning
- ProMotion® technology's light, quiet braided hose and swiveling ball joint make the pull-down sprayhead easier and more comfortable to use
- MasterClean™ sprayface features an easy-to-clean surface that withstands mineral buildup and maximizes spray performance
- High-arch spout offers vertical clearance for tall cookware and pitchers
- Single lever handle is simple to use and makes adjusting water temperature easy
- 1.5 gpm (5.7 lpm) maximum flow rate at 60 psi (4.14 bar)
- Temperature memory allows faucet to be turned on and off at the temperature set during prior usage
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance
- DockNetik® secure docking system locks sprayhead into place when not in use



Sustainability

WATER-SAVING DESIGN

Available Colors/Finishes

Color tiles intended for reference only.

	CP	Polished Chrome
	VS	Vibrant Stainless
	BL	Matte Black
	2MB	Vibrant Brushed Moderne Brass

+001-800-456-4537
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to la.kohler.com/en for Mexico/Latin America or www.kohler.com USA.
11-03-2026 16:32 - MX

THE BOLD LOOK OF KOHLER

Codes/Standards

ADA, CSA B651 compliant when installed to the specific requirements of these regulations.

ADA CSA B651

ASME A112.18.1/CSA B125.1
NSF/ANSI/CAN 372
NSF/ANSI/CAN 61
DOE - Energy Policy Act 1992
California Energy Commission (CEC)
ADA
ICC/ANSI A117.1
CSA B651

Technical Information

All product dimensions are nominal.

Handle

Handle Style/Type:	Lever

Spout

Spout Reach:	8-9/16" (217 mm)

Flow Rate

Faucet Flow Rate:	1.5 gpm (5.7 l/min)

Valves

Included Valve:	Ceramic disc

Material

- Premium metal construction for durability and reliability
- KOHLER finishes resist corrosion and tarnishing

Recommended Products/Accessories

- K-77685 Single-cartridge water filtration system
- K-77686 Double-cartridge water filtration system
- K-77687 Single replacement filter cartridge
- K-77688 Two-pack replacement filter cartridges

Optional Products/Accessories

- 1012715 Deep Rough-In


Warranty

See website for detailed warranty information.

KOHLER® Faucet Lifetime Limited Warranty

+001-800-456-4537
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to la.kohler.com/en for Mexico/Latin America or www.kohler.com USA.
11-03-2026 16:32 - MX

THE BOLD LOOK OF KOHLER.



Installation

- Single-hole or three-hole installation (escutcheon plate included)
- Flexible supply lines simplify installation

Installation Notes

Install this product according to the installation instructions.

ADA complaint for faucet handles only.
ADA compliant for faucet handles only
ADA, CSA B651 compliant when installed to the specific requirements of these regulations.

+001-800-456-4537
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to la.kohler.com/en for Mexico/Latin America or www.kohler.com USA.
11-03-2026 16:32 - MX

THE BOLD LOOK OF KOHLER