## **KOHLER** Faucets

# Single-handle bar sink faucet K-22975

#### **Features**

- High-arch swing spout with 150° rotation offers superior clearance for filling pitchers, chilling bottles, and cleanup
- Single lever handle makes adjusting water temperature easy.
- Temperature memory allows faucet to be turned on and off at the temperature set during prior usage
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance
- 1.5 gpm (5.7 lpm) maximum flow rate at 60 psi (4.14 bar)

#### Material

- Premium metal construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing

#### Installation

- Single-hole or three-hole installation (escutcheon plate included)
- Flexible supply lines simplify installation

### Adapters, Rough-in and Extension Kits

1327990 Range: 2-1/2" (64 mm) - 4-13/16" (122 mm)

#### Recommended Products/Accessories

K-77685 Single-cartridge water filtration system K-77686 Double-cartridge water filtration system K-77687 single replacement filter cartridge K-77688 Replacement Filter Cartridges, Two-Pack

#### **Optional Products/Accessories**

1012715 Kitchen Faucet Deep Rough-In Kit



ADA CSA B651

#### Codes/Standards

ASME A112.18.1/CSA B125.1 NSF/ANSI/CAN 61 NSF/ANSI/CAN 372 All applicable US Federal and State material regulations DOE - Energy Policy Act 1992 California Energy Commission (CEC) ADA ICC/ANSI A117.1 CSA B651 IAPMO Certification

## KOHLER® Faucet Lifetime Limited Warranty


See website for detailed warranty information.

#### **Available Colors/Finishes**

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome
	VS	Vibrant® Stainless
	BL	Matte Black
	2MB	Vibrant® Brushed Moderne
		Brass





#### **Technical Information**

All product dimensions are nominal.

Faucet:

Flow rate: 1.5 gal/min (5.7 l/min)

Drain included: No

Spout:

Spout reach: 7-7/8" (200 mm)

Handshower:

Rated maximum 0 gal/min (0 l/min)

flow:

**Pressure/fixture Supply Requirements** 

Fixture pressure 125 psi (861.8 kPa)

max (static):

Fixture pressure min 20 psi (137.9 kPa)

(static):

#### **Notes**

Install this product according to the installation instructions.

ADA compliant for faucet handles only ADA, CSA B651 compliant when installed to the specific requirements of these regulations.

