

KOHLER® Faucets

Non-thermostatic bath and shower faucet, 17.2 lpm
Toobi™
K-23147IN-4

Features

- Modern, simplistic exposed mixing valve serves as a hub for bath and shower controls
- Premium glass storage tray is convenient for holding personal items
- Lever handle with red and blue indexing
- Simple, intuitive push-button control toggles between bath filler and shower outlet
- Unique slotted spout fills bath with a no-splash cascading flow
- 4.5 gpm (17.2 lpm) maximum flow rate at 43.5 psi (3.0 bar)
- Coordinates with Toobi faucets, accessories, and showering components to complete your bathroom
- Showerhead sold separately

Material

- Premium material construction for durability and reliability

Installation

- Wall-mount
- G 1/2 connection



Codes/Standards

None Applicable


KOHLER® India Faucet Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome



Technical Information

All product dimensions are nominal.

Drain included: No

Notes

Install this product according to the installation guide.