


Features

- One-piece toilets integrate the tank and bowl into a seamless, easy-to-clean design
- Elongated bowl offers added room and comfort
- Smooth and rounded edges help prevent injury
- Rim-to-floor height: 15-9/16" (395 mm)
- Top-mount dual-flush actuator offers a choice of 0.8 or 1.28 gpf (3.0 or 4.8 lpf)
- 2" (51 mm) plastic trapway
- Fully skirted trapway simplifies cleaning
- Revolution 360™ flushing technology generates a forceful swirling motion to keep the bowl clean longer
- Seat and lid sold separately

Installation

- Floor-mount/floor outlet
- Standard 12" (305 mm) S-trap rough-in
- Requires connection to toilet water supply line. All hoses and connections are included

**Codes/Standards**



None Applicable

See website for detailed warranty information.




Family Care™

One-piece elongated toilet with skirted trapway,
dual-flush
K-23188K-NS




Use a 45° double wye fitting.

Do not use a double sanitary tee.



Front of Bowl



Technical Information

All product dimensions are nominal.

Toilet type: Floor-mount
Waste Outlet: Floor
Flush type: Revolution 360
Trap passageway: 1-15/16" (49 mm)
Rim to water surface: 6-1/4" (158 mm)
Rough-in: 12" (305 mm)

Notes

Install this product according to the installation instructions.