


Features

- One-piece toilets integrate the tank and bowl into a seamless, easy-to-clean design
- Elongated bowl offers added room and comfort
- Smooth and rounded edges help prevent injury
- Rim-to-floor height: 15-9/16" (395 mm)
- Top-mount dual-flush actuator offers a choice of 0.8 or 1.28 gpf (3.0 or 4.8 lpf)
- 2" (51 mm) ceramic trapway
- Fully skirted trapway simplifies cleaning
- Revolution 360™ flushing technology generates a forceful swirling motion to keep the bowl clean longer
- Hidden cord design conceals bidet seat cords (bidet seat sold separately)

Installation


- Floor-mount/floor outlet
- Standard 12" (305 mm) S-trap rough-in
- Requires connection to toilet water supply line. All hoses and connections are included



Codes/Standards

None Applicable

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Toilet type:	Floor-mount
Waste Outlet:	Floor
Flush type:	Revolution 360
Trap passageway:	1-15/16" (49 mm)
Rim to water surface:	6-1/4" (158 mm)
Rough-in:	12" (305 mm)

Notes

Install this product according to the installation instructions.