



Family Care™


One-piece elongated toilet with skirted trapway,
dual-flush
K-23188X-NS

Features

- One-piece toilets integrate the tank and bowl into a seamless, easy-to-clean design
- Elongated bowl offers added room and comfort
- Smooth and rounded edges help prevent injury
- Rim-to-floor height: 15-9/16" (395 mm)
- Top-mount dual-flush actuator offers a choice of 0.8 or 1.28 gpf (3.0 or 4.8 lpf)
- 2" (51 mm) ceramic trapway
- Fully skirted trapway simplifies cleaning
- Revolution 360™ flushing technology generates a forceful swirling motion to keep the bowl clean longer
- Seat and lid sold separately

Installation

- Floor-mount/floor outlet
- Standard 12" (305 mm) S-trap rough-in
- Requires connection to toilet water supply line. All hoses and connections are included



Codes/Standards

None Applicable

See website for detailed warranty information.

Call Center: +66 (2) 204-6000

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to <http://www.kohler.co.th>.


11-12-2025 01:48 - TH

THE BOLD LOOK
OF **KOHLER**®



Family Care™

One-piece elongated toilet with skirted trapway,
dual-flush
K-23188X-NS



Technical Information

All product dimensions are nominal.

Toilet type: Floor-mount

Waste Outlet: Floor

Flush type: Revolution 360

Trap passageway: 1-15/16" (49 mm)

Rim to water

from water surface:

Notes

Notes
Install this product according to the installation instructions.