



Family Care™


Hidden cord two-piece elongated toilet with skirted
trapway, dual-flush
K-23191K-HC

Features

- Two-piece design
- Elongated bowl offers added room and comfort
- Smooth and rounded edges help prevent injury
- Rim-to-floor height: 15-3/8" (390 mm)
- Top-mount dual-flush actuator offers a choice of 0.8 or 1.28 gpf (3.0 or 4.8 lpf)
- 1-15/16" (49 mm) fully glazed trapway
- Revolution 360™ flushing technology generates a forceful swirling motion to keep the bowl clean longer
- Skirted trapway simplifies cleaning
- Hidden cord design conceals bidet seat cords (bidet seat sold separately)

Installation

- Standard 12" (305 mm) rough-in
- Supply line sold separately



Codes/Standards

Plumbing Standards
GB 25502

See website for detailed warranty
information.

+86-21-2606-2000

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to <http://www.kohlerasiapacific.com>.


11-12-2025 01:50 - PH

THE BOLD LOOK
OF **KOHLER**[®]



Family Care™

Hidden cord two-piece elongated toilet with skirted trapway, dual-flush
K-23191K-HC



Technical Information

All product dimensions are nominal.

Toilet type:	Floor-mount
Waste Outlet:	Floor
Flush type:	Revolution 360
Trap passageway:	1-15/16" (49 mm)
Rim to water surface:	6-1/4" (158 mm)
Rough-in:	12" (305 mm)

Notes

Install this product according to the installation instructions.