



**Family Care™**

Two-piece elongated toilet with skirted trapway,  
dual-flush  
**K-23191K-NS**

### Features

- Two-piece design
- Elongated bowl offers added room and comfort
- Smooth and rounded edges help prevent injury
- Rim-to-floor height: 15-3/8" (390 mm)
- Top-mount dual-flush actuator offers a choice of 0.8 or 1.28 gpf (3.0 or 4.8 lpf)
- 1-15/16" (49 mm) fully glazed trapway
- Class Five™ and Revolution 360™ technologies generate powerful flush with swirling motion
- Skirted trapway simplifies cleaning

### Installation

- Standard 12" (305 mm) rough-in
- Seat and supply line sold separately



### Codes/Standards



None Applicable

See website for detailed warranty information.



Family Care™

Two-piece elongated toilet with skirted trapway,  
dual-flush  
**K-23191K-NS**



## Technical Information

All product dimensions are nominal.

Toilet type:	Floor-mount
Waste Outlet:	Floor
Flush type:	Class Five, Revolution 360
Trap passageway:	1-15/16" (49 mm)
Rim to water surface:	6-1/4" (158 mm)
Rough-in:	12" (305 mm)

## Notes

Install this product according to the installation instructions.