



Family Care™
Two-piece elongated toilet with skirted trapway,
dual-flush
K-23191K-S

Features


- Two-piece design
- Elongated bowl offers added room and comfort
- Smooth and rounded edges help prevent injury
- Rim-to-floor height: 15-3/8" (390 mm)
- Top-mount dual-flush actuator offers a choice of 0.8 or 1.28 gpf (3.0 or 4.8 lpf)
- 1-15/16" (49 mm) fully glazed trapway
- Fully skirted trapway simplifies cleaning
- Siphonic flushing system
- Revolution 360™ flushing technology generates a forceful swirling motion to keep the bowl clean longer
- Quiet-Close™ elongated lid and seat prevents slamming
- French Curve™ design with square rear enhances ergonomic comfort
- Quick-Release™ functionality allows seat to be removed easily from toilet for convenient cleaning

Material

- Plastic seat

Installation

- Standard 12" (305 mm) rough-in
- Supply line sold separately




Codes/Standards

None Applicable

See website for detailed warranty information.

KOHLER®

Family Care™ Two-piece elongated toilet with skirted trapway, dual-flush K-23191K-S



Technical Information

All product dimensions are nominal.

Toilet type:	Floor-mount
Waste Outlet:	Floor
Flush type:	Revolution 360
Trap passageway:	1-15/16" (49 mm)
Rim to water surface:	6-1/4" (158 mm)
Rough-in:	12" (305 mm)

Notes

Install this product according to the installation instructions.