



Family Care™


Hidden cord two-piece elongated toilet with skirted trapway, dual-flush
K-23191MY-HC

Features

- Two-piece design
- Elongated bowl offers added room and comfort
- Smooth and rounded edges help prevent injury
- Rim-to-floor height: 15-3/8" (390 mm)
- Top-mount dual-flush actuator offers a choice of 0.8 or 1.28 gpf (3.0 or 4.8 lpf)
- 1-15/16" (49 mm) fully glazed trapway
- Revolution 360™ flushing technology generates a forceful swirling motion to keep the bowl clean longer
- Skirted trapway simplifies cleaning
- Hidden cord design conceals bidet seat cords (bidet seat sold separately)

Installation

- Standard 12" (305 mm) rough-in
- Supply line sold separately



Codes/Standards


None Applicable

See website for detailed warranty information.




Family Care™


Hidden cord two-piece elongated toilet with skirted trapway, dual-flush
K-23191MY-HC



For Back-to-Back Toilet Installations




Use a 45° double wye fitting.



Do not use a double sanitary tee

Front of Bowl



Technical Information

All product dimensions are nominal.

Toilet type: Floor-mount
Waste Outlet: Floor
Flush type: Revolution 360
Trap passageway: 1-15/16" (49 mm)
Rim to water surface: 6-1/4" (158 mm)
Rough-in: 12" (305 mm)

Notes

Install this product according to the installation instructions.