

Features

- Derived from historical references this lighting collection is intricate and modern at the same time
- Suitable for living, dining, and kitchen spaces, allowing you to create a cohesive design aesthetic throughout your home
- Candelabra base (E12) socket, works best with type G or T light bulbs (sold separately)
- A 10' (3.1 m) cord offers many height options

Material

- Manufactured with quality materials and complemented with a meticulous finishing process
- Durable finishes engineered to last and designed to coordinate with KOHLER faucet finishes

Recommended Products/Accessories

K-23723 Faucet cleaner




Codes/Standards

UL 1598
CSA C22.2 No. 250.0
cETL Listed
ETL Listed

KOHLER® Indoor Lighting Fixtures Limited Warranty

See website for detailed warranty information.



Required Electrical Service

One circuit required.

Lights: 120 V, 1 A, 60 Hz

Technical Information

All product dimensions are nominal.

Material: Brass
 Number of Lights: 3
 Lighting Type: Socket-based
 Socket Type: E-12 Candelabra
 Number of Shades: 3
 Shade Type: Glass - clear
 Hanging Type: Cord
 Height: $32\text{-}5/8"$ (828 mm) - $152\text{-}5/8"$ (3876 mm)
 Electrical component rating: Socket Rating: 60 Hz, 60 W, 1350 Lumens, 3000K