



Damask® | K-23346-CH05

37" linear chandelier

Features

- Derived from historical references this lighting collection is intricate and modern at the same time
- Suitable for living, dining, and kitchen spaces, allowing you to create a cohesive design aesthetic throughout your home
- Candelabra base (E12) socket, works best with type G or T light bulbs (sold separately)
- Includes installation hardware



1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
7-30-2026 01:52 - US-CA

THE BOLD LOOK
OF **KOHLER**

Codes/Standards

CSA C22.2 No. 250.0
cETL Listed
ETL Listed

Warranty

See website for detailed warranty information.

KOHLER® Indoor Lighting Fixtures Limited Warranty

Technical Information

All product dimensions are nominal.

Number of Lights:	5
Lighting Type:	Socket-based
Socket Type:	E-12 Candelabra
Number of Shades:	5
Hanging Type:	Downrod
Height:	18-3/4" (477 mm) - 34-15/16" (887 mm)

Material

- Manufactured with quality materials and complemented with a meticulous finishing process
- Durable finishes engineered to last and designed to coordinate with KOHLER faucet finishes

Recommended Products/Accessories

K-23723 Faucet cleaner

Required Electrical Service


One circuit required.

Lights: 120 V, 60 Hz

Electrical Component Ratings

Socket Rating: 60 Hz, 60 W, 2250 Lumens





Installation Notes

Install this product according to the installation instructions.

