

### Features

- A single handle controls both on/off activation and temperature setting
- 4" (102 mm) spout height
- 4-1/2" (114 mm) spout reach
- 4.0 gpm (15.0 lpm) maximum flow rate at 43.5 psi (3.0 bar)
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance
- Coordinates with other products in the Parallel collection

### Material

- Premium metal construction for durability and reliability
- KOHLER finishes resist corrosion and tarnishing

### Installation

- Single hole
- Preattached flexible supply lines simplify installation



### Codes/Standards

None Applicable


### KOHLER® Faucet Lifetime Limited Warranty

See website for detailed warranty information.

### Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
	CP	Polished Chrome
	AF	Vibrant® French Gold
	BN	Vibrant® Brushed Nickel
	BV	Vibrant® Brushed Bronze
	BL	Matte Black
	BRD	Vibrant Brushed Rose Gold
	RGD	Vibrant Rose Gold



### Technical Information

All product dimensions are nominal.

Faucet flow rate: 2.2 gal/min (8.3 l/min)

### Spout:

Spout reach: 4-1/2" (114 mm)

### Notes

Install this product according to the installation instructions.