

### Features


- Versatile, contemporary design
- Single Lever handle allows for on/off activation, volume, and temperature control
- For use with cold water line only
- 4-7/16" (113 mm) spout reach
- 4-11/16" (101 mm) spout height
- 2.2 gpm (8.3 lpm) maximum flow rate at 65 psi (4.5 bar)
- Directionally adjustable, laminar-flow aerator
- Stationary spout
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance
- Drain sold separately
- Coordinates with other products in the Parallel collection
- Ideal for vessel sink applications

### Material

- Premium brass construction for durability and reliability
- KOHLER finishes resist corrosion and tarnishing

### Installation


- Single hole
- Preattached flexible supply lines simplify installation



### Codes/Standards

Plumbing Standards  
TIS 2067-2552

See website for detailed warranty information.



**Technical Information**

All product dimensions are nominal.

Faucet flow rate: 1.849 gal/min (7 l/min)

Drain with overflow: Yes

**Spout:**

Spout reach: 4-1/2" (115 mm)

**Notes**

Install this product according to the installation instructions.