

Features

- Versatile, contemporary design
- Single Lever handle allows for on/off activation, volume, and temperature control
- Red/blue indexing on handle
- 4-9/16" (116 mm) spout reach
- 4-1/8" (105 mm) spout height
- Aerated flow
- Stationary spout
- 2.2 gpm (8.3 lpm) maximum flow rate at 45 psi (3.1 bar)
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance
- Metal pop-up drain with lift rod and tailpiece
- Coordinates with other products in the Parallel collection
- Ideal for vessel sink applications

Material

- Premium metal construction for durability and reliability
- KOHLER finishes resist corrosion and tarnishing

Installation

- Single hole
- Preattached flexible supply lines simplify installation



Codes/Standards


Plumbing Standards
GB 18145

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome
	AF	Vibrant® French Gold
	BN	Vibrant® Brushed Nickel
	BL	Matte Black



Technical Information

All product dimensions are nominal.

Faucet flow rate: 1.84 gal/min (7 l/min)

Drain included: Yes

Spout:

Spout reach: 4-1/2" (115 mm)

Notes

Install this product according to the installation instructions.