## **KOHLER**, Faucets

Widespread bathroom sink faucet, 1.2 gpm K-23484-4

#### **Features**

- Two Lever handles offer separate control of hot and cold water
- 5" (127 mm) spout reach
- 1.2 gpm (4.5 lpm) maximum flow rate at 60 psi (4.14 bar)
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance
- Metal pop-up drain with lift rod and 1-1/4" tailpiece
- Coordinates with other products in the Parallel collection

### Material

- Premium metal construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing

## Installation

- Three-hole installation for 8" 16" centers
- Flexible supply lines and quick-connect fittings simplify installation

## **Recommended Products/Accessories**

K-23726 Drain treatment

K-23723 Faucet cleaner

K-21897 Double toilet paper holder

K-23524 18" towel bar

K-23525 24" towel bar

K-23526 Towel arm

K-23527 Vertical toilet paper holder

K-23528 Pivoting toilet paper holder

K-23529 Robe hook





## Codes/Standards

ASME A112.18.1/CSA B125.1 NSF/ANSI/CAN 61 NSF/ANSI/CAN 372

All applicable US Federal and State material

regulations
DOE - Energy Policy Act 1992

EPA WaterSense®

California Energy Commission (CEC)

ADA

ICC/ANSI A117.1

**CSA B651** 

OBC

**IAPMO** Certification

# KOHLER® Faucet Lifetime Limited Warranty


See website for detailed warranty information.

## **Available Colors/Finishes**

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome
	SN	Vibrant® Polished Nickel
	AF	Vibrant® French Gold
	BN	Vibrant® Brushed Nickel
	BV	Vibrant® Brushed Bronze





## **Technical Information**

All product dimensions are nominal.

Faucet:

Flow rate: 1.2 gal/min (4.5 l/min)

Drain included: Yes
Drain with overflow: Yes

Spout:

Spout reach: 5" (127 mm)

Handshower:

Rated maximum 0 gal/min (0 l/min)

flow:

## **Notes**

Install this product according to the installation instructions.

ADA compliant for handles only.

ADA, OBC, CSA B651 compliant when installed to the specific requirements of these regulations.

