

Features

- Versatile, contemporary design
- Two Lever handles offer separate control of hot and cold water
- Red/blue indexing on handles
- 5-1/16" (129 mm) spout reach
- 5-1/4" (133 mm) spout height
- Aerated flow
- Stationary spout
- 2.2 gpm (8.3 lpm) maximum flow rate at 45 psi (3.1 bar)
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance
- Metal pop-up drain with lift rod and tailpiece
- Coordinates with other products in the Parallel collection

Material

- Premium metal construction for durability and reliability
- KOHLER finishes resist corrosion and tarnishing

Installation


- Widespread
- For 8" – 16" (203 – 406 mm) centers
- Handles are preassembled on valves to simplify installation
- Preattached flexible supply lines simplify installation



Codes/Standards

Plumbing Standards
GB 18145

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Faucet flow rate: 2.2 gal/min (8.3 l/min)

Drain included: Yes

Drain with overflow: Yes

Spout:

Spout reach: 5" (128 mm)

Notes

Install this product according to the installation instructions.