

Features


- Single lever handle allows for both on/off activation and temperature setting
- Red/blue indexing on handle
- 6-1/2" (165 mm) spout reach
- Aerated flow
- Stationary spout
- 2.2 gpm (8.3 lpm) maximum flow rate at 45 psi (3.1 bar)
- Includes metal pop-up drain with 1-1/4" (32 mm) tailpiece
- Coordinates with other products in the Parallel collection
- Trim only, requires valve to complete installation

Material

- Premium metal construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing

Installation


- Wall-mount
- Requires wall-mount K-28028T valve (sold separately)



Codes/Standards

Plumbing Standards
GB 18145

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Faucet:

Flow rate: 1.75 gal/min (6.6 l/min)

Drain included: Yes

Drain with overflow: Yes

Spout:

Spout reach: 7-1/4" (184 mm)

Notes

Install this product according to the installation guide.