

### Features

- A single handle controls both on/off activation and temperature setting
- 6.45 inch (164 mm) spout reach
- 2.38 gpm (9.0 lpm) maximum flow rate at 43.5 psi (3.0 bar)
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance
- Coordinates with other products in the Parallel collection

### Material

- Premium metal construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing

### Installation

- Wall-mount
- Preattached flexible supply lines simplify installation



### Codes/Standards

None Applicable



### KOHLER® India Faucet Limited Warranty

See website for detailed warranty information.

### Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
	CP	Polished Chrome
	AF	Vibrant® French Gold
	BN	Vibrant® Brushed Nickel
	BL	Matte Black
	RGD	Vibrant Rose Gold



### Technical Information

All product dimensions are nominal.

Drain included: No

Drain with overflow: No

### Notes

Install this product according to the installation guide.