

Features

- Versatile, contemporary design
- Single Lever handle allows for on/off activation, volume, and temperature control
- Nondiverter bath spout
- Stationary spout
- 4" (102 mm) spout reach
- 8.2 gpm (31 lpm) maximum bath faucet flow rate at 45 psi (3.1 bar)
- Diverter switches water flow from bath fill to handshower, and returns to bath fill position when water is turned off
- Includes Shift™+ handshower and 60" (1500 mm) shower hose
- Multifunction handshower offers full coverage and targeted massage spray settings
- Ergonomic design is easy to use
- 2.2 gpm (8.3 lpm) maximum handshower flow rate at 45 psi (3.1 bar)
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance
- Coordinates with other products in the Parallel collection

Material

- Premium material construction for durability and reliability

Installation


- Deck-mount
- Four-hole installation



Codes/Standards

Plumbing Standards
GB 18145

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Faucet flow rate: 8.2 gal/min (31 l/min)

Spout:

Spout reach: 8-1/4" (209 mm)

Handshower rated max flow: 2.2 gal/min (8.3 l/min)

Notes

Install this product according to the installation instructions.