

Features

- Versatile, contemporary design
- Single Lever handle allows for on/off activation, volume, and temperature control
- Red/blue indexing on handle
- Stationary spout
- 8-11/16" (220 mm) spout reach
- 13.4 gpm (50.7 lpm) maximum bath faucet flow rate at 45 psi (3.1 bar)
- Diverter switches water flow from bath fill to handshower, and returns to bath fill position when water is turned off
- Includes Shift™+ handshower and 60" (1500 mm) shower hose
- Multifunction handshower offers full coverage and targeted massage spray settings
- Ergonomic design is easy to use
- 2.5 gpm (9.5 lpm) handshower maximum flow rate at 80 psi (5.5 bar)
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance
- Coordinates with other products in the Parallel collection

Material

- Premium metal construction for durability and reliability
- KOHLER finishes resist corrosion and tarnishing

Installation


- Valves included
- Floor-mount
- Requires K-97905T mounting-block (sold separately)



Codes/Standards

Plumbing Standards
GB 18145

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Faucet flow rate: 13.4 gal/min (50.7 l/min)

Spout:

Spout reach: 8-11/16" (221 mm)

Handshower rated max flow: 2.5 gal/min (9.5 l/min)

Notes

Install this product according to the installation instructions.