

Features

- 4" (102 mm) centerset faucet holes
- Classic rectangular basin
- Overflow drain
- Combination consists of the K-2358-4 basin and the K-2357 pedestal
- Coordinates with other products in the Archer collection

Material

- Vitreous china

Installation

- Pedestal

Recommended Products/Accessories

- K-7605-P Angle Supply with Stop (pair)
- K-8998 P-Trap
- K-23726 Drain treatment
- K-23725 Cast iron cleaner

Included Components

- K-2357 Bathroom Sink Pedestal
- K-2358-4 24" rectangular pedestal bathroom sink



Codes/Standards




ASME A112.19.2/CSA B45.1
IAPMO Certification

KOHLER® Vitreous China Bathroom Sink Lifetime Limited Warranty

See website for detailed warranty information.


Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	0	White
	96	Biscuit
	7	Black Black™



Archer®
24" rectangular pedestal bathroom sink
K-2359-4



Technical Information

All product dimensions are nominal.

- Basin configuration: Single Bowl
Center(s): 4" (102 mm)
Bowl area (Only): Length: 16-1/4" (413 mm)
Width: 11-15/16" (303 mm)
Water depth: 4" (102 mm)
With overflow: Yes
Number of deck holes: 3
Faucet hole(s): 1-1/4" (32 mm)
Drain hole: 1-3/4" (44 mm)

Notes

Install this product according to the installation instructions.