



Modern Farm | K-23662-CH03

23-1/2" chandelier

Features

- Suitable for living, dining, and kitchen spaces, allowing you to create a cohesive design aesthetic throughout your home
- Candelabra base (E12) socket, works best with type G16.5 white, clear or Edison bulbs (sold separately)
- Downrods offer additional height options



Codes/Standards

CSA C22.2 No. 250.0
cETL Listed
ETL Listed

Technical Information

All product dimensions are nominal.

Number of Lights:	3
Lighting Type:	Socket-based
Socket Type:	E-12 Candelabra
Number of Shades:	3
Hanging Type:	Downrod
Downrod Detail:	1 x 18-13/16" (478 mm)
Height:	11-3/16" (284 mm) - 65-3/16" (1656 mm)

Material

- Manufactured with quality materials and complemented with a meticulous finishing process
- Durable finishes engineered to last and designed to coordinate with KOHLER faucet finishes

Required Electrical Service

One circuit required.

Lights: 120 V, 60 Hz


Electrical Component Ratings

Socket Rating: 60 Hz, 60 W

Warranty

See website for detailed warranty information.





Installation Notes

Install this product according to the installation instructions.

