



Modern Farm | K-23665-SC03

Three-light sconce

Features

- Suitable for any living space, allowing you to create a cohesive design aesthetic throughout your home
- Candelabra base (E12) socket, works best with type G16.5 white, clear or Edison bulbs (sold separately)
- Can be mounted vertically or horizontally
- Shades swivel, enabling you to direct light where you need it
- Suitable for damp locations, per UL 1598



Codes/Standards

CSA C22.2 No. 250.0

cETL Listed

ETL Listed

Technical Information

All product dimensions are nominal.

Number of Lights:	3
Lighting Type:	Socket-based
Socket Type:	E-12 Candelabra
Number of Shades:	3
Hanging Type:	Non-hanging

Material

- Manufactured with quality materials and complemented with a meticulous finishing process
- Durable finishes engineered to last and designed to coordinate with KOHLER faucet finishes

Required Electrical Service

One circuit required.

Lights: 120 V, 1.5 A, 60 Hz

Electrical Component Ratings

Socket Rating: 60 Hz, 60 W

Warranty

See website for detailed warranty information.




1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.

7-30-2026 01:58 - US-CA



Installation Notes

Install this product according to the installation instructions.

