

Features

- A perfect complement to our Memoirs suite of products
- Frosted glass shades perfectly diffuse the light, reducing glare in the bathroom
- Medium base (E26) socket, works best with type G light bulbs (sold separately)
- Includes installation hardware
- Suitable for damp locations, per UL 1598
- Fixture is dimmable when paired with dimmer switch and compatible bulbs

Material

- Manufactured with quality materials and complemented with a meticulous finishing process
- Durable finishes engineered to last and designed to coordinate with KOHLER faucet finishes

Recommended Products/Accessories

K-23723 Faucet cleaner



Codes/Standards




UL 1598
CSA C22.2 No. 250.0
cETL Listed
ETL Listed


KOHLER® Indoor Lighting Fixtures Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	SNL	Polished Nickel
	BNL	Brushed Nickel
	CPL	Polished Chrome



Required Electrical Service

One circuit required.

Lights: 120 V, 1 A, 60 Hz

Technical Information

All product dimensions are nominal.

Material: Brass
Number of Lights: 2
Lighting Type: Socket-based
Socket Type: E-26 Medium
Number of Shades: 2
Shade Type: Glass - frosted
Hanging Type: Non-hanging
Electrical component rating: Socket Rating: 60 Hz, 60 W, 1600 Lumens, 3000K