

### Features

- A perfect complement to our Memoirs suite of products
- Frosted glass shades perfectly diffuse the light, reducing glare in the bathroom
- Medium base (E26) socket, works best with type G light bulbs (sold separately)
- Suitable for damp locations, per UL 1598

### Material

- Manufactured with quality materials and complemented with a meticulous finishing process
- Durable finishes engineered to last and designed to coordinate with KOHLER faucet finishes

### Recommended Products/Accessories

K-23723 Faucet cleaner



### Codes/Standards




UL 1598  
CSA C22.2 No. 250.0  
cETL Listed  
ETL Listed


### KOHLER® Indoor Lighting Fixtures Limited Warranty

See website for detailed warranty information.

### Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
	SNL	Polished Nickel
	BNL	Brushed Nickel
	CPL	Polished Chrome



## Required Electrical Service

One circuit required.

Lights: 120 V, 2 A, 60 Hz

## Technical Information

All product dimensions are nominal.

Material: Brass

Number of Lights: 4

Lighting Type: Socket-based

Socket Type: E-26 Medium

Number of Shades: 4

Shade Type: Glass - frosted

Hanging Type: Non-hanging

Electrical component rating: Socket Rating: 60 Hz, 60 W, 3200 Lumens, 3000K