

KOHLER® Faucets

Wall-mount bathroom sink faucet spout with Ribbon design, 7.0 lpm
K-23888T

Features

- Stationary spout
- 9-11/16" (246 mm) spout reach
- 1.85 gpm (7.0 lpm) maximum flow rate at 60 psi (4.14 bar)
- Includes drain
- Coordinates with Components faucets, accessories, and showering components to complete your bathroom

Material

- Brass
- KOHLER® finishes resist corrosion and tarnishing

Installation

- Wall-mount

Required Products/Accessories

K-77980-4 Wall-mount bathroom sink faucet handle

or

K-77980-4A Wall-mount bathroom sink faucet handle

or

K-T77981-4 Wall-mount bathroom sink faucet Lever handle trim

or

K-T77981-8 Wall-mount bathroom sink faucet Oyl handle trim

or

K-T77981-9 Wall-mount bathroom sink faucet Industrial handle trim

Recommended Products/Accessories

K-23726 Drain treatment

K-23723 Faucet cleaner

Optional Products/Accessories

K-7107 Decorative Drain

K-7108 Decorative Drain

K-7114 Pop-Up Drain

K-7127 Drain

K-7129 Drain

K-33151 Clicker drain without overflow




Codes/Standards

Plumbing Standards
GB 18145

See website for detailed warranty information.

KOHLER Faucets **Components™**

Wall-mount bathroom sink faucet spout with Ribbon design, 7.0 lpm
K-23888T



Technical Information

All product dimensions are nominal.

Faucet:

Flow rate: 1.85 gal/min (7 l/min)

Drain included: Yes

Drain with overflow: Yes

Notes

Install this product according to the installation instructions.