

Features

- A single handle controls both on/off activation and temperature setting
- 2-13/32" (61 mm) spout height
- 4-5/8" (117 mm) spout reach
- 1.8 gpm (7.0 lpm) maximum flow rate at 43.5 psi (3.0 bar)

Material

- Premium metal construction for durability and reliability
- KOHLER finishes resist corrosion and tarnishing

Installation

- Single hole
- Drain sold separately



Codes/Standards

None Applicable


KOHLER® India Faucet Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome
	AF	Vibrant® French Gold
	BL	Matte Black
	RGD	Vibrant Rose Gold



Technical Information

All product dimensions are nominal.

Drain included: No

Drain with overflow: No

Notes

Install this product according to the installation guide.