

Features

- Rectangular basin
- 4" (102 mm) centerset faucet holes
- Overflow drain
- Combines with the K-24052 pedestal to create the K-24050-4 Kelston pedestal sink
- Coordinates with other products in the Kelston collection

Material

- Vitreous china

Installation

- Pedestal

Recommended Products/Accessories

- K-23726 Drain treatment
- K-23725 Cast iron cleaner
- K-24052 Pedestal sink base



Codes/Standards

ASME A112.19.2/CSA B45.1
IAPMO Certification

KOHLER® Vitreous China Bathroom Sink Lifetime Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
-------	------	-------------

	0	White
---	---	-------

No image available.
This product is a component and not intended to be a standalone installation.

Technical Information

All product dimensions are nominal.

Basin configuration:	Single Bowl
Center(s):	4" (102 mm)
Bowl area:	Length: 14-5/16" (364 mm) Width: 13" (330 mm) Bowl depth: 5-1/8" (130 mm) Water depth: 3-1/16" (77 mm)
With overflow:	Yes
Number of deck holes:	3
Faucet hole(s):	4" (102 mm)

Notes

Install this product according to the installation instructions.