

Features

- Sleek, minimalist design
- Advanced spray engine provides two alternate experiences: full coverage rain with Katalyst™ air-induction technology and laminar stream
- Full coverage rain with Katalyst™ air-induction technology delivers a drenching spray experience, ideal for rinsing shampoo from hair
- Laminar flow
- Flexible, silicone nozzles assure long life and easy clean
- MasterClean™ sprayface features an easy-to-clean surface that withstands mineral buildup and maximizes spray performance
- Optimized sprayface for maximum performance
- 2.64 gpm (12.0 lpm) maximum flow rate at 80 psi (5.5 bar)

Material

- Premium material construction for durability and reliability
- KOHLER finishes resist corrosion and tarnishing

Technology

- Katalyst™ air-induction technology infuses water with air, creating bigger drops for a more powerful spray

Installation

- Requires two-function rainhead arm and flange (sold separately)
- Wall- or ceiling-mount



Codes/Standards






None Applicable


KOHLER® India Faucet, Sanitaryware and Bathing Products Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome
	AF	Vibrant® French Gold
	BV	Vibrant® Brushed Bronze
	BL	Matte Black
	RGD	Vibrant Rose Gold



Technical Information

All product dimensions are nominal.

Showerhead/Body Spray:

Rated maximum flow: 3.17 gal/min (12 l/min)

Notes

Install this product according to the installation guide.