

### Features

- Advanced spray engine provides three alternate experiences: full coverage, powerful massage, and Komotion™ care spray
- Full coverage with Katalyst™ air-induction technology offers a drenching spray experience, ideal for rinsing shampoo from hair
- Powerful massage spray is a focused stream that targets sore muscles, or use as a utility spray to rinse kids, pets, and your shower
- Komotion™ spray delivers a soothing, circular water pattern
- Simple thumb button allows for a smooth transition between sprays
- 5 inch (126 mm) diameter sprayface
- MasterClean™ sprayface features an easy-to-clean surface that withstands mineral buildup and maximizes spray performance
- 4.38 gpm (16.6 lpm) maximum flow rate at 43.5 psi (3.0 bar)
- Requires hose and wall-mount holder (sold separately)

### Material

- Premium metal construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing

### Installation

- G 1/2 inlet connection



### Codes/Standards





None Applicable



### KOHLER® India Faucet, Sanitaryware and Bathing Products Limited Warranty

See website for detailed warranty information.

### Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
	CP	Polished Chrome
	AF	Vibrant® French Gold
	BV	Vibrant® Brushed Bronze
	RGD	Vibrant Rose Gold



### Technical Information

All product dimensions are nominal.

### Notes

Install this product according to the installation instructions.