

Features

- Single-function showerhead with 48 nozzle 5" (127 mm) diameter sprayface
- Optimized sprayface for maximum performance
- MasterClean™ sprayface features an easy-to-clean surface that withstands mineral buildup and maximizes spray performance
- 1.25 gpm (4.7 lpm) maximum flow rate at 45 psi (3.1 bar)
- Requires shower arm and flange (sold separately)
- Coordinates with other products in the Parallel collection

Material

- Premium material construction for durability and reliability
- KOHLER finishes resist corrosion and tarnishing

Technology

- Katalyst® Plus air-induction technology infuses water with double the ratio of air to water as regular Katalyst®, creating even more invigorating droplets at a 1.25 gpm flow rate

Installation

- 1/2" -14 NPT connection
- Wall-mount

Recommended Products/Accessories

K-7397 Shower Arm and Flange



Codes/Standards

ASME A112.18.1/CSA B125.1
DOE - Energy Policy Act 1992
EPA WaterSense®
California Energy Commission (CEC)


KOHLER® Faucet Lifetime Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome
	BN	Vibrant® Brushed Nickel
	BL	Matte Black
	2MB	Vibrant® Brushed Moderne Brass



Technical Information

All product dimensions are nominal.

Spout:

Shower/Rainhead rated max flow: 1.25 gal/min (4.7 l/min)

Notes

Install this product according to the installation instructions.