

Features

- Ideal for commercial installations
- Antimicrobial finish inhibits the growth of mold-, mildew-, stain-, and odor-causing bacteria on the fixture surface. This product does not protect users against bacteria, viruses, or other disease organisms. Always clean and wash this product thoroughly before and after each use
- Elongated bowl offers added room and comfort
- 2-1/8" (54 mm) fully glazed trapway
- Combines with a K-25100, K-25100-RA, K-25100-T or K-25100-TR tank to create a complete K-25087-SS, K-25087-SSRA, K-25087-SST or K-25087-SSTR Kingston™ two-piece toilet



Installation

- Three-bolt quick-connect installation
- Standard 12" (305 mm) rough-in
- Seat sold separately

Recommended Products/Accessories

K-23726 Drain treatment



Codes/Standards

ASME A112.19.2/CSA B45.1

EPA WaterSense®

IAPMO Certification


KOHLER® Toilets and Seats Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
-------	------	-------------

	0	White
---	---	-------

No image available.
This product is a component and not intended to be a standalone installation.

Technical Information

All product dimensions are nominal.

Toilet type:	Floor-mount
Waste Outlet:	Floor
Bowl shape:	Elongated
Trap passageway:	2-1/8" (54 mm)
Water surface size:	10-13/16" x 7-1/4" (274 mm x 183 mm)
Rim to water surface:	5-5/8" (143 mm)
Rough-in:	12" (305 mm)

Notes

Install this product according to the installation instructions.