



Kingston™

Round-front toilet bowl
K-25096

Features

- Ideal for commercial installations
- 2-1/8" (54 mm) fully glazed trapway
- Combines with a K-25100, K-25100-RA, K-25100-T or K-25100-TR tank to create a complete K-25097, K-25097-RA, K-25097-T or K-25097-TR Kingston™ two-piece toilet

Installation

- Three-bolt quick-connect installation
- Standard 12" (305 mm) rough-in
- Seat sold separately

Recommended Products/Accessories

K-23726 Drain treatment



Codes/Standards

ASME A112.19.2/CSA B45.1

EPA WaterSense®

IAPMO Certification


KOHLER® Toilets and Seats Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
-------	------	-------------

	0	White
---	---	-------

1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.kohler.com USA or www.kohler.ca Canada

7-3-2024 20:23 - US

THE BOLD LOOK
OF **KOHLER**®

No image available.
This product is a component and not intended to be a standalone installation.

Technical Information

All product dimensions are nominal.

Toilet type:	Floor-mount
Waste Outlet:	Floor
Bowl shape:	Round-front
Flush type:	Gravity siphon jet
Trap passageway:	2-1/8" (54 mm)
Water surface size:	10-3/8" x 7-1/16" (264 mm x 179 mm)
Rim to water surface:	5-5/8" (143 mm)
Rough-in:	12" (305 mm)

Notes

Install this product according to the installation instructions.