



# Kingston™

Toilet tank, 1.28 gpf  
K-25100-T

## Features

- Ideal for commercial installations
- 1.28 gpf (4.8 lpf)
- Durable metal left-hand Polished Chrome trip lever
- Tank cover locks included
- Combines with a K-25076 or K-25076-SS bowl to create a complete K-25077-T or K-25077-SST Kingston two-piece toilet
- Class Five® canister optimizes the flow out of the tank, harnessing gravity and the natural powerful reducing cascade of water to increase the power and effectiveness of the flush



## Installation

- Three-bolt quick-connect installation
- Supply line sold separately

## Recommended Products/Accessories

K-23726 Drain treatment



## Codes/Standards

ASME A112.19.2/CSA B45.1

EPA WaterSense®

IAPMO Certification


## KOHLER® Toilets and Seats Limited Warranty

See website for detailed warranty information.

## Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
-------	------	-------------

	0	White
---	---	-------



**Kingston™**  
Toilet tank, 1.28 gpf  
**K-25100-T**

No image available.  
This product is a component and not intended to be a standalone installation.

### Technical Information

All product dimensions are nominal.

Toilet type: Bowl-mount  
Waste Outlet: Floor  
Flush type: Class Five

### Notes

Install this product according to the installation instructions.