



Kingston™

Toilet tank, 1.28 gpf
K-25100

Features

- Ideal for commercial installations
- 1.28 gpf (4.8 lpf)
- Durable metal left-hand Polished Chrome trip lever
- Combines with a K-25076 or K-25076-SS bowl to create a complete K-25077 or K-25077-SS Kingston two-piece toilet
- Class Five® canister optimizes the flow out of the tank, harnessing gravity and the natural powerful reducing cascade of water to increase the power and effectiveness of the flush

Installation

- Three-bolt quick-connect installation
- Supply line sold separately

Recommended Products/Accessories

K-23726 Drain treatment



Codes/Standards

ASME A112.19.2/CSA B45.1

EPA WaterSense®

IAPMO Certification

KOHLER® Toilets and Seats Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
-------	------	-------------

	0	White
---	---	-------

1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.kohler.com USA or www.kohler.ca Canada

7-3-2024 20:37 - US

THE BOLD LOOK
OF **KOHLER**®



Kingston™
Toilet tank, 1.28 gpf
K-25100

No image available.
This product is a component and not intended to be a standalone installation.

Technical Information

All product dimensions are nominal.

Toilet type: Bowl-mount
Waste Outlet: Floor
Flush type: Class Five

Notes

Install this product according to the installation instructions.
Install this product according to the installation instructions.