

KOHLER® Faucets

Single-handle bathroom sink faucet with Lever handle,

4.5 lpm

K-25102T-4E2

Features


- Single Lever handle allows for on/off activation, volume, and temperature control
- Red/blue indexing on handle
- 3-15/16" (100 mm) spout reach
- 3-5/16" (84 mm) spout height
- 1.2 gpm (4.5 lpm) maximum flow rate at 60 psi (4.14 bar)
- Aerated flow
- KOHLER ceramic disc valves exceed industry longevity standards by over two times, ensuring durable performance for life
- Includes cable drain with 1-1/4" (32 mm) metal tailpiece
- Part of the Aleo S bathroom faucet and showering collection

Material

- Premium metal construction for durability and reliability
- KOHLER finishes resist corrosion and tarnishing

Installation

- Deck-mount
- For single-hole installation
- Flexible supply lines simplify installation



Codes/Standards

None Applicable

KOHLER® Faucet Lifetime Limited Warranty

See website for detailed warranty information.


KOHLER Faucets

Single-handle bathroom sink faucet with Lever handle,

4.5 lpm

K-25102T-4E2

Aleo™ S



Technical Information

All product dimensions are nominal.

Faucet flow rate: 1.2 gal/min (4.5 l/min)

Drain included: Yes

Drain with overflow: Yes

Notes

Install this product according to the installation instructions.