

Features

- Single lever handle allows for both on/off activation and temperature setting
- 3-15/16" (100 mm) spout reach
- 3-5/16" (84 mm) spout height
- 2.2 gpm (8.3 lpm) maximum flow rate at 60 psi (4.14 bar)
- Aerated flow delivers a smooth, steady stream of water
- Red/blue indexing on handle
- Includes valve
- KOHLER ceramic disc valves exceed industry longevity standards by over two times, ensuring durable performance for life
- Includes cable drain with 1-1/4" (32 mm) metal tailpiece
- Part of the Aleo S bathroom faucet and showering collection

Material

- Premium metal construction for durability and reliability
- KOHLER[®] finishes resist corrosion and tarnishing

Installation

- Deck-mount
- For single-hole installation
- Flexible supply lines simplify installation

Recommended Products/Accessories


K-23723 Faucet cleaner



Codes/Standards

Plumbing Standards
GB 18145

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Faucet:

Flow rate: 1.2 gal/min (4.5 l/min)

Pressure: 45 psi (3.1 bar)

Drain included: Yes

Drain with overflow: Yes

Notes

Install this product according to the installation instructions.