

Features

- Single Lever handle allows for on/off activation, volume, and temperature control
- Red/blue indexing on handle
- 5-15/16" (151 mm) spout reach
- 8-3/10" (211 mm) spout height
- 1.2 gpm (4.5 lpm) maximum flow rate at 60 psi (4.14 bar)
- Aerated flow
- KOHLER ceramic disc valves exceed industry longevity standards by over two times, ensuring durable performance for life
- Clicker drain with tailpiece
- Part of the Aleo S bathroom faucet and showering collection

Material


- Premium metal construction for durability and reliability
- KOHLER finishes resist corrosion and tarnishing

Installation

- Deck-mount
- For single-hole installation
- Flexible supply lines simplify installation

Recommended Products/Accessories

K-23726 Drain treatment




Codes/Standards

None Applicable

KOHLER® Faucet Lifetime Limited Warranty

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Faucet flow rate: 1.2 gal/min (4.5 l/min)

Drain included: Yes

Drain with overflow: Yes

Spout:

Spout reach: 5-15/16" (151 mm)

Notes

Install this product according to the installation instructions.