

# KOHLER® Faucets Tower single-handle bathroom sink faucet with lever

**Aleo™ S**  
handle, 8.3 lpm  
**K-25104T-4**

## Features

- Single lever handle allows for both on/off activation and temperature setting
- 5-15/16" (151 mm) spout reach
- 10-7/16" (266 mm) spout height
- 2.2 gpm (8.3 lpm) maximum flow rate at 60 psi (4.14 bar)
- Aerated flow delivers a smooth, steady stream of water
- Red/blue indexing on handle
- Includes valve
- KOHLER ceramic disc valves exceed industry longevity standards by over two times, ensuring durable performance for life
- Includes clicker drain with 1-1/4" (32 mm) metal tailpiece
- Part of the Aleo S bathroom faucet and showering collection

## Material

- Premium metal construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing

## Installation

- Deck-mount
- For single-hole installation
- Flexible supply lines simplify installation

## Recommended Products/Accessories

K-23726 Drain treatment  
K-23723 Faucet cleaner



## Codes/Standards


Plumbing Standards  
GB 18145

See website for detailed warranty information.

# KOHLER Faucets

## Aleo™ S

Tower single-handle bathroom sink faucet with lever handle, 8.3 lpm  
K-25104T-4



### Technical Information

All product dimensions are nominal.

#### Faucet:

Flow rate: 1.2 gal/min (4.5 l/min)

Drain included: Yes

Drain with overflow: Yes

#### Spout:

Spout reach: 5-15/16" (151 mm)

### Notes

Install this product according to the installation instructions.