

Features

- Single Lever handle allows for both volume and temperature control
- Unique rear handle mounting creates floating effect and simplifies cleaning
- Available in a range of dazzling finishes
- 164 mm (6.47 inch) spout reach
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance

Material

- Premium metal construction for durability and reliability
- KOHLER finishes resist corrosion and tarnishing

Installation

- Deck-mount
- For single-hole installation
- Preattached flexible supply lines simplify installation



Codes/Standards

None Applicable


KOHLER® India Faucet Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome
	AF	Vibrant® French Gold
	BL	Matte Black
	RGD	Vibrant Rose Gold



Technical Information

All product dimensions are nominal.

Faucet flow rate: 2.98 gal/min (11.3 l/min)

Spout:

Spout reach: 6-7/16" (164 mm)

Handle clearance: 1-1/4" (32 mm)

Notes

Install this product according to the installation instructions.