

Features

- Single Lever handle allows for both volume and temperature control
- Unique one-piece design creates a continuous look and simplifies installation
- Available in a range of dazzling finishes
- 7-1/2" (191 mm) spout reach
- 2.1 gpm (8.0 lpm) maximum flow rate at 45 psi (3.1 bar)
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance

Material

- Premium metal construction for durability and reliability
- KOHLER finishes resist corrosion and tarnishing

Installation

- Wall-mount
- Preattached flexible supply lines simplify installation

Required Products/Accessories

K-5679IN Single-handle wall-mount bathroom sink faucet valve



Codes/Standards

None Applicable



KOHLER® India Faucet Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome
	AF	Vibrant® French Gold
	BL	Matte Black
	RGD	Vibrant Rose Gold



Technical Information

All product dimensions are nominal.

Faucet flow rate: 1.98 gal/min (7.5 l/min)

Spout:

Spout reach: 7-1/2" (191 mm)

Notes

Install this product according to the installation instructions.