

## Features

- Apron designed to fit in standard 30" (762 mm) apron-front cabinetry
- Single bowl
- 9-1/2" (241 mm) depth provides generous workspace
- Offset drain increases workspace in the sink and storage space underneath
- Self-Trimming® apron overlaps cabinet face for easy installation and beautiful results
- Matte finish offers rich, dimensional color

## Material

- KOHLER Neoroc composite material is thermal shock-resistant and heat-resistant to 750°F (399°C)
- Color-dense Neoroc material helps to minimize the appearance of scratches and stains

## Installation

- Undermount

## Recommended Products/Accessories

- K-8801 Sink drain and strainer with tailpiece
- K-8799 Sink drain and strainer basket

## Optional Products/Accessories

- K-11352 Disposal Flange with Stopper
- K-9000 P-Trap

## Included Components

- K-26026 Farmhouse kitchen sink towel hook
- K-30181 Stainless steel sink racks



## Codes/Standards





CSA B45.5/IAPMO Z124




## KOHLER® Neoroc® Sinks Lifetime Limited Warranty

See website for detailed warranty information.

## Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
	CM7	Matte Graphite
	CM4	Matte Grey
	CM2	Matte Brown
	CM1	Matte Black



### Technical Information

All product dimensions are nominal.

Basin configuration: Single Bowl

Min. base cabinet width: 30" (762 mm)

Bowl area (Only):  
Length: 24-1/2" (622 mm)  
Width: 17-5/8" (447 mm)  
Bowl depth: 9-1/2" (241 mm)  
Water depth: 9-1/2" (241 mm)

Template: Undermount, 1477787-7, required, included

### Notes

Install this product according to the installation instructions.