

Features

- Apron designed to fit in standard 30" (762 mm) apron-front cabinetry
- Single bowl
- 9-1/2" (241 mm) depth provides generous workspace
- Offset drain increases workspace in the sink and storage space underneath
- Self-Trimming® apron overlaps cabinet face for easy installation and beautiful results
- Matte finish offers rich, dimensional color

Material

- KOHLER Neoroc composite material is thermal shock-resistant and heat-resistant to 750°F (399°C)
- Color-dense Neoroc material helps to minimize the appearance of scratches and stains

Installation

- Undermount

Recommended Products/Accessories


- K-8801 Sink drain and strainer with tailpiece
- K-8799 Sink drain and strainer basket

Optional Products/Accessories

- K-11352 Disposal Flange with Stopper
- K-9000 P-Trap

Included Components

- K-26026 Farmhouse kitchen sink towel hook
- K-30181 Stainless steel sink racks



Codes/Standards





CSA B45.5/IAPMO Z124
IAPMO Certification




KOHLER® Neoroc® Sinks Lifetime Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CM7	Matte Graphite
	CM4	Matte Grey
	CM2	Matte Brown
	CM1	Matte Black



Technical Information

All product dimensions are nominal.

Basin configuration: Single Bowl

Min. base cabinet width: 30" (762 mm)

Bowl area (Only):
Length: 24-1/2" (622 mm)
Width: 17-5/8" (447 mm)
Bowl depth: 9-1/2" (241 mm)
Water depth: 9-1/2" (241 mm)

Template: Undermount, 1477787-7, required, included

Notes

Install this product according to the installation instructions.