

KOHLER® Faucets

Single-handle bathroom sink faucet, cold only, 16.0 lpm

Beam™
K-26042IN-4

Features

- Versatile modern design
- Single handle provides on/off activation and volume control
- For use with cold water line only
- 3.94 inch (100 mm) spout reach
- 3.46 inch (88 mm) spout height
- 4.22 gpm (16.0 lpm) maximum flow rate at 43.5 psi (3.0 bar)
- Aerated flow
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance

Material

- Premium material construction for durability and reliability
- KOHLER finishes resist corrosion and tarnishing

Installation

- Single-hole installation
- Deck-mount



Codes/Standards

None Applicable


KOHLER® India Faucet Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome



Technical Information

All product dimensions are nominal.

Drain included: No

Drain with overflow: No

Notes

Install this product according to the installation guide.