



Bolero®
16-3/4" oval drop-in/undermount bathroom sink, no
overflow
K-2611-SU

Features

- Oval basin
- Satin finish
- No faucet holes; requires wall- or counter-mount faucet

Material

- Premium 20-gauge stainless steel

Installation

- Drop-in or undermount

Recommended Products/Accessories

- K-8998 P-Trap
- K-23726 Drain treatment
- K-23729 Stainless steel cleaner

Included Components

- 1193643 Basin clamps
- 1193643 Basin clamps



ADA

CSA B651

OBC

Codes/Standards

ASME A112.19.3/CSA B45.4

ADA

ICC/ANSI A117.1


CSA B651

OBC


IAPMO Certification

**KOHLER® One-Year Limited
Warranty**

See website for detailed warranty information.



Note: Waterproof unprotected overhang area of the underside of wood counter.



	A
Drop-in (shown)	7" (178 mm)
Under-mount	7-3/4" (197 mm)

Technical Information

All product dimensions are nominal.

- Basin configuration: Single Bowl
- Bowl area (Only): Length: 15" (381 mm)
Width: 10" (254 mm)
Water depth: 5-1/2" (140 mm)
- With overflow: No
- Drain hole: 1-5/8" (41 mm)
- Template: 111579-7, required, included

Notes

Install this product according to the installation instructions.

ADA, OBC, CSA B651 compliant when installed to the specific requirements of these regulations.